

DuPont™ ProShield® 20 , *PBCHF5SWH00*



Technical Data Sheet

DuPont ProShield® 20 White. Hooded coverall. Stitched external seams. Elasticated wrists, ankles and face. Elasticated waist (stitched-in). Zipper flap. White.

Certifications

- Certified according to Regulation (EU) 2016/425
- Chemical protective clothing, Category III, Type 5 and 6
- EN 1073-2 (protection against radioactive contamination)
- Antistatic treatment (EN 1149-5) - on both sides

Packaging(Quantity/Box)

50 per box, individually packed.

Product Size	Article Number	Body Height(cm)	Chest Girth(cm)	Chest Girth(in)	Body Height(ft/in)
SM	D15338118	162-170	84-92	33-36	5'4"-5'7"
MD	D15338122	168-176	92-100	36-39	5'6"-5'9"
LG	D15338134	174-182	100-108	39-43	5'8"-6'0"
XL	D15338149	180-188	108-116	43-46	5'11"-5'2"
2X	D15338157	186-194	116-124	46-49	6'1"-6'4"
3X	D15338160	192-200	124-132	49-52	6'3"-6'7"

Reference Number: PBCHF5SWH00

PHYSICAL PROPERTIES

Property	Test Method	Result	EN Class
Abrasion Resistance ⁷	EN 530 Method 2	>10 cycles	1 of 6 ¹
Basis Weight	DIN EN ISO 536	43 g/m ²	N/A
Colour	N/A	White	N/A
Exposure to high Temperature	N/A	Melting point ~165 °C	N/A
Flex Cracking Resistance ⁷	EN ISO 7854 Method B	>1000 cycles	1 of 6 ¹
Puncture Resistance	EN 863	>5 N	1 of 6 ¹
Resistance to Water Penetration	DIN EN 20811	3 kPa	N/A
Surface Resistance at RH 25%, inside ⁷	EN 1149-1	< 2,5 • 10 ⁹ Ohm	N/A
Surface Resistance at RH 25%, outside ⁷	EN 1149-1	< 2,5 • 10 ⁹ Ohm	N/A
Tensile Strength (MD)	DIN EN ISO 13934-1	>30 N	1 of 6 ¹
Tensile Strength (XD)	DIN EN ISO 13934-1	>30 N	1 of 6 ¹
Trapezoidal Tear Resistance (MD)	EN ISO 9073-4	>10 N	1 of 6 ¹
Trapezoidal Tear Resistance (XD)	EN ISO 9073-4	>10 N	1 of 6 ¹

1 According to EN 14325 2 According to EN 14126 3 According to EN 1073-2 4 According to EN 14116 12 According to EN 11612 5 Front Tyvek ® / Back 6 Based on test according to ASTM D-572 7 See Instructions for Use for further information, limitations and warnings > Larger than < Smaller than N/A Not Applicable STD DEV Standard Deviation

GARMENT PERFORMANCE

Property	Test Method	Result	EN Class
Nominal protection factor ⁷	EN 1073-2	>5	1 of 3 ³
Seam Strength	EN ISO 13935-2	>50 N	2 of 6 ¹
Shelf Life ⁷	N/A	3 years ⁶	N/A
Type 5: Inward Leakage ¹¹	EN ISO 13982-2	14 %	N/A
Type 5: Inward Leakage of Airborne Solid Particulates	EN ISO 13982-2	Pass ⁷	N/A
Type 6: Resistance to Penetration by Liquids (Low Level Spray Test)	EN ISO 17491-4, Method A	Pass	N/A

1 According to EN 14325 3 According to EN 1073-2 12 According to EN 11612 13 According to EN 11611 5 Front Tyvek ® / Back 6 Based on test according to ASTM D-572 7 See Instructions for Use for further information, limitations and warnings 11 Based on the average of 10 suits, 3 activities, 3 probes > Larger than < Smaller than N/A Not Applicable * Based on lowest single value

PENETRATION AND REPELLENCY

Property	Test Method	Result	EN Class
Repellency to Liquids, Sodium Hydroxide (10%)	EN ISO 6530	>80 %	1 of 3 ¹
Repellency to Liquids, Sulphuric Acid (30%)	EN ISO 6530	>95 %	3 of 3 ¹
Resistance to Penetration by Liquids, Sodium Hydroxide (10%)	EN ISO 6530	<5 %	2 of 3 ¹
Resistance to Penetration by Liquids, Sulphuric Acid (30%)	EN ISO 6530	<5 %	2 of 3 ¹

¹ According to EN 14325 > Larger than < Smaller than

Important Note

The permeation data published have been generated for DuPont by independent accredited testing laboratories according to the test method applicable at that time (EN369, ASTM F739, EN 374-3, EN ISO 6529 (method A and B) or ASTM D6978)

The data is typically the average of three fabrics samples tested.

All chemicals have been tested at an assay of greater than 95 (w/w) % unless otherwise stated.

The tests were performed at room temperature and environmental pressure unless otherwise stated.

A different temperature may have significant influence on the breakthrough time.

Permeation typically increases with temperature.

Cumulative permeation data have been measured or have been calculated based on steady state permeation rate.

Cytostatic drugs testing has been performed at a test temperature of 27°C according to ASTM D6978 or ISO 6529 with the additional requirement of reporting a normalized breakthrough time at 0.01 µg/cm²/min.

Chemical warfare agents (Lewisite, Sarin, Soman, Mustard, Tabun and VX Nerve Agent) have been tested according to MIL-STD-282 at 22°C or according to FINABEL 0.7 at 37°C.

Permeation data for Tyvek®; is applicable to white Tyvek®; 500/ Tyvek®; 600 only and is not applicable for other Tyvek®; styles or colours.

Permeation data are usually measured for single chemicals. The permeation characteristics of mixtures can often deviate considerably from the behaviour of the individual chemicals.

Please use the permeation data provided as a part of the risk assessment to assist with the selection of a protective fabric, garment or accessory suitable for your application. Breakthrough time is not the same as safe wear time. Breakthrough times are indicative of the barrier performance, but results can vary between the test methods and laboratories. Breakthrough time alone is insufficient to determine how long a garment may be worn once the garment has been contaminated. Safe user wear time may be longer or shorter than the breakthrough time depending on the permeation behaviour of the substance, the toxicity of the substance, working conditions and the exposure conditions (e.g. temperature, pressure, concentration, physical state).

Latest Update Permeation Data: 30/05/2018

The permeation data published have been generated for DuPont by independent accredited testing laboratories according to the test method applicable at that time (EN ISO 6529 (method A and B), ASTM F739, ASTM F1383, ASTM D6978, EN 374, EN ISO 6529 (method A and B) or ASTM D6978)

The data is typically the average of three fabrics samples tested.

All information provided is based on our current knowledge of the subject at the date of this publication. This information may be subject to revision as new knowledge and experience becomes available. The data provided fall within the normal range of product properties and relate only to the specific material designated; these data may not be valid for such material used in combination with any other materials or additives or in any process, unless expressly indicated otherwise. The data provided should not be used to establish specification limits or used alone as the basis of design; they are not intended to substitute for any testing you may need to conduct to determine for yourself the suitability of a specific material for your particular purposes. Since DuPont cannot anticipate all variations in actual end-use conditions DuPont makes no warranties and assumes no liability in connection with any use of this information. Nothing in this publication is to be considered as a license to operate under or a recommendation to infringe any patent rights.

The permeation data published have been generated for DuPont by independent accredited testing laboratories according to the test method applicable at that time (EN ISO 6529 (method A and B), ASTM F739, ASTM F1383, ASTM D6978, EN 374, EN ISO 6529 (method A and B) or ASTM D6978)

The data is typically the average of three fabrics samples tested.

All information provided is based on our current knowledge of the subject at the date of this publication. This information may be subject to revision as new knowledge and experience becomes available. The data provided fall within the normal range of product properties and relate only to the specific material designated; these data may not be valid for such material used in combination with any other materials or additives or in any process, unless expressly indicated otherwise. The data provided should not be used to establish specification limits or used alone as the basis of design; they are not intended to substitute for any testing you may need to conduct to determine for yourself the suitability of a specific material for your particular purposes. Since DuPont cannot anticipate all variations in actual end-use conditions DuPont makes no warranties and assumes no liability in connection with any use of this information. Nothing in this publication is to be considered as a license to operate under or a recommendation to infringe any patent rights.

Cumulative permeation data have been measured or have been calculated based on minimum detectable permeation rate.

Cytostatic drugs testing has been performed at a test temperature of 27°C according to ASTM D6978 or ISO 6529 with the additional requirement of reporting a normalized breakthrough time at 0.01 µg/cm²/min.

Chemical warfare agents (Lewisite, Sarin, Soman, Mustard, Tabun and VX Nerve Agent) have been tested according to MIL-STD-282 at 22°C or according to FINABEL 0.7 at 37°C.

Permeation data for Tyvek® is applicable to white Tyvek® 500 and Tyvek® 600 only and is not applicable for other Tyvek® styles or colours.

Permeation data are usually measured for single chemicals. The permeation characteristics of mixtures can often deviate considerably from the behaviour of the individual chemicals.

The permeation data for gloves published have been generated according to ASTM F739 and to ASTM F1383.

The degradation data for gloves published have been generated based on a gravimetric method.

This degradation testing exposes one side of the glove material to the test chemical for four hours. The percent weight change after exposure is measured at four time intervals: 5, 30, 60 and 240 minutes.

Degradation Ratings:

- E: EXCELLENT (0-10% Weight Change)
- G: GOOD (11-20% Weight Change)
- F: FAIR (21-30% Weight Change)
- P: POOR (31-50% Weight Change)
- NR: NOT RECOMMENDED (Above 50% Weight Change)
- NT: NOT TESTED

Degradation is the physical change in a material after chemical exposure. Typical observable effects may be swelling, wrinkling, deterioration, or delamination. Strength loss may also occur.

Please use the permeation data provided as a part of the risk assessment to assist with the selection of a protective fabric, garment, glove or accessory suitable for your application.

Breakthrough time is not the same as safe wear time. Breakthrough times are indicative of the barrier performance, but results can vary between the test methods and laboratories. Breakthrough time alone is insufficient to determine how long a garment may be worn once the garment has been contaminated. Safe user wear time may be longer or shorter than the breakthrough time depending on the permeation behaviour of the substance, the toxicity of the substance, working conditions and the exposure conditions (e.g. temperature, pressure, concentration, physical state).

Latest Update Permeation Data: 15/03/2019

The information provided herein corresponds to our knowledge on the subject at the date of its publication. This information may be subject to revision as new knowledge and experience becomes available. The data provided fall within the normal range of product properties and relate only to the specific material designated; these data may not be valid for such material used in combination with any other materials or additives or in any process, unless expressly indicated otherwise. The data provided should not be used to establish specification limits or used alone as the basis of design; they are not intended to substitute for any testing you may need to conduct to determine for yourself the suitability of a specific material for your particular purposes. Since DuPont cannot anticipate all variations in actual end-use conditions DuPont makes no warranties and assumes no liability in connection with any use of this information. Nothing in this publication is to be considered as a license to operate under or a recommendation to infringe any patent rights.

For further product information, literature and as well as assistance in locating a local supplier, please visit:

www.safespec.dupont.co.uk

The footnotes can be found on the SafeSPEC® website.

Copyright © DuPont. All rights reserved. The DuPont Oval Logo, DuPont®, The miracles of science® and all products denoted with ® or ™ are registered trademarks or trademarks of E. I. du Pont de Nemours and Company or its affiliates.

DuPont Personal Protection

DuPont de Nemours (Luxembourg) S.à.r.l.

L-2984 Luxembourg

Tel.: +800 3666 6666 (international toll-free)

Fax: +352 3666 5071

E-mail: personal.protection@lux.dupont.com